

The AccuMix-ML™ makes quick work of blending highly-viscous formula components together, providing a thorough, tool-free means of mixing.



## AccuMix™ ML

After the AccuBlend-HV™ doses a formula into a GFI Eco-Line™ pail, the pail is dropped into the mated pot found on the AccuMix-ML. From there, about five minutes is all it takes to get ink that's thoroughly mixed and ready for press. The G5 pails can be used multiple times if longer runs require more ink.

### Features

- Eco-Line G5 Pail with lid - holds 5 pounds (2.27 kg)
- Patent-pending orbital radial bearing system
- Integrated pot computer-mated to Eco-Line G5 Pails
- Dual clamp-down lid
- Digital timer
- Variable speed

### Ink Types:

### Container:

### Capacity:

### Speed Control:

### Mixing Speed:

### Dimensions:

### Power Requirements:

### Shipping Weight:

All types of highly-viscous paste ink  
Eco-Line G5 Pail  
5 pounds (2.27 kg)  
Variable (100 - 1,750 rpm)  
About 8 minutes for a 5 pound batch  
18" (45.7 cm) W x 27" (68.5 cm)  
H x 14" (35.5 cm) D  
120VAC, 60Hz, 8A  
Approximately 175 pounds (79 kg)



GFI Innovations 847-263-9000 GFIis.com  
2940 Miller Dr., Plymouth, IN 46563 USA